

Product data sheet

Specifications



Non-Reversing Starter Size 1, 3-Pole, Motor Logic SSOLR (Class 10), NEMA 4/4X

8536SCW13V03H10

⚠ Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Solid state Motor Logic class 10
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Coil Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Terminal Type	Screw clamp terminals

Environment

Enclosure Type	NEMA 4/4X brushed stainless steel
Certifications	UL Listed CSA NEMA

Ordering and shipping details

Category	21203-8502,36 W/STAINLESS ENCLOSURES
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Weight	50.00 lb(US) (22.68 kg)

Contractual warranty

Warranty	18 months
----------	-----------