

Product data sheet

Specifications



NEMA Motor Starter, Type S, nonreversing, Size 1, 27A, 10 HP at 460 VAC, 5 kA SCCR, 2 phase, 4 pole, melting alloy, 208 VAC coil, NEMA 4/4X

8536SCW14V08

⚠ To be discontinued

⚠ To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|---------------|---------------|
| Product Type | Motor starter |
| Product Range | S |
| Starter Type | Non reversing |

Complementary

| | |
|------------------------|--|
| Nema Size | 1 |
| Rated Current | 27 A |
| Number Of Poles | 4P |
| Maximum Voltage Rating | 600 V AC |
| Phase | 2 phases |
| Type Of Overload | Melting alloy 2 |
| Horsepower Rating | 7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC |
| Scrr | Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC |
| Coil Voltage | 208 V AC 60 Hz |
| Control Circuit Type | Common control circuit |
| Control Units | No control units |
| Pilot Light | Without pilot light |
| Auxiliary Contacts | Without |
| Terminal Type | Screw clamp terminals |
| Height | 13.19 in (335.03 mm) |
| Width | 6.38 in (162.05 mm) |
| Depth | 7.81 in (198.37 mm) |

Environment

| | |
|----------------|-----------------------------------|
| Enclosure Type | NEMA 4/4X brushed stainless steel |
|----------------|-----------------------------------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|----------------|--------------------------|
| Certifications | UL Listed CSA NEMA |
|----------------|--------------------------|

Ordering and shipping details

| | |
|-------------------|--|
| Category | 21203 - 8502,36 W/STAINLESS ENCLOSURES |
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | MX |

Packing Units

| | |
|------------------------------|--------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 13.19 in (33.5 cm) |
| Package 1 Width | 6.38 in (16.2 cm) |
| Package 1 Length | 7.80 in (19.8 cm) |
| Package 1 Weight | 33.25 lb(US) (15.082 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Pvc Free

| | |
|---------------------------|---|
| Eu Rohs Directive | Not compliant |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |