

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 2, 3-Pole, Melting Alloy Overload, Open +Options

8536SDO1V02SX22Y342

Price\*: 1,818.00 USD

! Discontinued

### Main

|               |               |
|---------------|---------------|
| Product Type  | Starter       |
| Product Range | S             |
| Starter Type  | Non reversing |

### Complementary

|                        |                                                                      |
|------------------------|----------------------------------------------------------------------|
| Nema Size              | 2                                                                    |
| Rated Current          | 45 A                                                                 |
| Number Of Poles        | 3P                                                                   |
| Maximum Voltage Rating | 600 V AC                                                             |
| Phase                  | 3 phase                                                              |
| Type Of Overload       | Melting alloy 3                                                      |
| Horsepower Rating      | 10 HP 200 V AC<br>15 HP 230 V AC<br>25 HP 460 V AC<br>25 HP 575 V AC |
| Coil Voltage           | 110 V AC 50 Hz<br>120 V AC 60 Hz                                     |
| Control Circuit Type   | Separate control circuit                                             |
| Control Units          | No control units                                                     |
| Auxiliary Contacts     | 2 NO + 2 NC                                                          |
| Terminal Type          | Screw clamp terminals                                                |

### Environment

|                |                          |
|----------------|--------------------------|
| Enclosure Type | Not rated (open device)  |
| Certifications | NEMA<br>CSA<br>UL Listed |

### Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

