

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 3, 3-Pole, Motor Logic SSOLR (Class 10), NEMA 1

8536SEG1V83CFF4H10P1R174TX11

Discontinued

### Main

|               |               |
|---------------|---------------|
| Product Type  | Starter       |
| Product Range | S             |
| Starter Type  | Non reversing |

### Complementary

|                        |                                                                      |
|------------------------|----------------------------------------------------------------------|
| Nema Size              | 3                                                                    |
| Rated Current          | 90 A                                                                 |
| Number Of Poles        | 3P                                                                   |
| Maximum Voltage Rating | 600 V AC                                                             |
| Phase                  | 3 phase                                                              |
| Type Of Overload       | Solid state Motor Logic class 10                                     |
| Horsepower Rating      | 25 HP 200 V AC<br>30 HP 230 V AC<br>50 HP 460 V AC<br>50 HP 575 V AC |
| Coil Voltage           | 480 V AC 60 Hz primary circuit<br>24 V AC 60 Hz secondary circuit    |
| Control Circuit Type   | Control circuit transformer                                          |
| Control Units          | Selector switch (HAND-OFF-AUTO)                                      |
| Pilot Light            | Red indicator on incandescent                                        |
| Auxiliary Contacts     | 1 NO + 1 NC                                                          |
| Other Equipment        | 2 fuses (primary), 1 fuse (secondary)                                |
| Terminal Type          | Screw clamp terminals                                                |

### Environment

|                |                            |
|----------------|----------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
| Certifications | NEMA<br>UL Listed<br>CSA   |

### Ordering and shipping details

|                   |                                  |
|-------------------|----------------------------------|
| Category          | 21193-8502,36 SE,SF(NOT S*R,T,W) |
| Discount Schedule | CP1                              |
| Returnability     | No                               |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|