

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 3, 3-Pole, Melting Alloy Overload +Options

8536SEO1V02SX11Y342

! Discontinued

### Main

|               |               |
|---------------|---------------|
| Product Type  | Starter       |
| Product Range | S             |
| Starter Type  | Non reversing |

### Complementary

|                        |  |
|------------------------|--|
| Nema Size              | 3  |
| Rated Current          | 90 A   |
| Number Of Poles        | 3P   |
| Maximum Voltage Rating | 600 V AC   |
| Phase                  | 3 phase  |
| Type Of Overload       | Melting alloy 3  |
| Horsepower Rating      | 25 HP 200 V AC<br>30 HP 230 V AC<br>50 HP 460 V AC<br>50 HP 575 V AC |
| Coil Voltage           | 110 V AC 50 Hz<br>120 V AC 60 Hz                                     |
| Control Circuit Type   | Separate control circuit   |
| Control Units          | No control units   |
| Auxiliary Contacts     | 1 NO + 1 NC  |
| Terminal Type          | Screw clamp terminals  |

### Environment

|                |                          |
|----------------|--------------------------|
| Enclosure Type | Not rated (open device)  |
| Certifications | UL Listed<br>NEMA<br>CSA |

### Ordering and shipping details

|                   |                                  |
|-------------------|----------------------------------|
| Category          | 21193-8502,36 SE,SF(NOT S*R,T,W) |
| Discount Schedule | CP1                              |
| Returnability     | No                               |
| Country Of Origin | MX                               |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|