

# Product data sheet

Specifications

SQUARE D



NEMA Motor Starter, Type S, nonreversing, Size 6, 540A, 400 HP at 460 VAC, 3 phase, 3 pole, melting alloy, 240 VAC coil, NEMA 12

8536SHA2V03

⚠ To be discontinued

⚠ To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Product Type	Motor starter
Product Range	S
Starter Type	Non reversing

## Complementary

Nema Size	6
Rated Current	540 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	150 HP 200 V AC 200 HP 230 V AC 400 HP 460 V AC 400 HP 575 V AC
Coil Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Control Circuit Type	Control circuit transformer
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Equipment	2 fuses (primary), 2 fuses (secondary)
Terminal Type	Screw clamp terminals
Height	65.00 in (1651.00 mm)
Width	20.22 in (513.59 mm)
Depth	13.00 in (330.20 mm)

## Environment

Enclosure Type	NEMA 12 painted sheet steel
----------------	-----------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Certifications	UL Listed CSA NEMA
----------------	--------------------------

## Ordering and shipping details

Category	21195 - 8502,36 SH,SJ(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	65.00 in (165.1 cm)
Package 1 Width	20.24 in (51.4 cm)
Package 1 Length	12.99 in (33.0 cm)
Package 1 Weight	42.00 lb(US) (19.051 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Not compliant
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>