

Product data sheet

Specifications

SQUARE D



NEMA Motor Starter, Type S, nonreversing, Size 7, 810A, 600 HP at 460 VAC, 3 phase, 3 pole, melting alloy, 480 VAC coil, open

8536SJO2V06

⚠ To be discontinued

⚠ To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Type	Motor starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	7
Rated Current	810 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Solid state Motor Logic class 20
Horsepower Rating	300 HP 230 V AC 600 HP 460 V AC 600 HP 575 V AC
Coil Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Control Circuit Type	Control circuit transformer
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Equipment	2 fuses (primary), 2 fuses (secondary)
Terminal Type	Screw clamp terminals
Height	37.25 in (946.15 mm)
Width	12.34 in (313.44 mm)
Depth	10.88 in (276.35 mm)

Environment

Enclosure Type	Not rated (open device)
Certifications	UL Listed CSA NEMA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	21195 - 8502,36 SH,SJ(NOT S*R,T,W)
Discount Schedule	CP1
Gtin	785901493402
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	148.00 lb(US) (67.132 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Reach Regulation	REACH Declaration
Eu Rohs Directive	Not compliant
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov