

Product data sheet

Specifications



COMBO STARTER 600VAC 18A NEMA

8538SBA21V84CF4P1P2TX11

Price*: 3,348.00 USD

⚠ Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	3 hp 200 V AC, 3 phase 3 hp 230 V AC, 3 phase 5 hp 460 V AC, 3 phase 5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent Green indicator off incandescent
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses primary circuit
Thermal Overload Type	Melting alloy 3
Disconnect Type	Non-fusible disconnect switch
Nema Size	0

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
----------------	---

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications