

Product data sheet

Specifications

SQUARE D



COMBO STARTER 600VAC 18A NEMA

8538SBG12V84CF4P21TX22

Price*: 2,996.00 USD

! Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	3 hp 200 V AC, 3 phase 3 hp 230 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent push-to-test
Auxiliary Contacts	2 NO + 2 NC
Control Circuit Fusing	2 fuses primary circuit
Thermal Overload Type	Melting alloy 3
Disconnect Type	Fusible disconnect switch H, 30 A
Nema Size	0

Environment

Enclosure Type	NEMA 1 painted sheet steel with external reset
----------------	--

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications