

# Product data sheet

Specifications



## COMBO STARTER 600VAC 45A NEMA

8538SDA11V02AP1S

Price\*: 3,324.00 USD

! Discontinued

### Main

|                      |                          |
|----------------------|--------------------------|
| Product              | Combination Starter      |
| Type                 | S                        |
| Control Circuit Type | Separate control circuit |

### Complementary

|                         |  |
|-------------------------|--|
| Control Circuit Voltage | 110 V AC 50 Hz<br>120 V AC 60 Hz   |
| Starter Type            | Non reversing  |
| Number Of Poles         | 3P   |
| Horsepower Rating       | 10 hp 200 V AC, 3 phase<br>15 hp 230 V AC, 3 phase<br>25 hp 460 V AC, 3 phase<br>25 hp 575 V AC, 3 phase |
| Maximum Voltage Rating  | 600 V AC   |
| Control Units           | Push-button START)<br>Push-button STOP)  |
| Pilot Light             | Red indicator on incandescent  |
| Auxiliary Contacts      | Without  |
| Thermal Overload Type   | Melting alloy 3  |
| Disconnect Type         | Non-fusible disconnect switch  |
| Nema Size               | 2  |

### Environment

|                |  |
|----------------|--|
| Enclosure Type | NEMA 12 painted sheet steel without external reset |
|----------------|--|

### Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |

### Packing Units

|                              |                          |
|------------------------------|--------------------------|
| Unit Type Of Package 1       | PCE                      |
| Number Of Units In Package 1 | 1                        |
| Package 1 Weight             | 60.00 lb(US) (27.216 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|