

Product data sheet

Specifications



COMBO STARTER 600VAC 45A NEMA

8538SDA21V81AF4T

Price*: 3,531.00 USD

! Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	10 hp 200 V AC, 3 phase 15 hp 230 V AC, 3 phase 25 hp 460 V AC, 3 phase 25 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Push-button START) Push-button STOP)
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Thermal Overload Type	Melting alloy 3
Disconnect Type	Non-fusible disconnect switch
Nema Size	2

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
----------------	---

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	60.00 lb(US) (27.216 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------