

Product data sheet

Specifications



COMBO STARTER 600VAC 45A NEMA

8538SDA26V02AP2S

Price*: 3,380.00 USD

⚠ Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	15 hp 460 V AC, 3 phase 15 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Push-button START) Push-button STOP)
Pilot Light	Green indicator off incandescent
Auxiliary Contacts	Without
Thermal Overload Type	Melting alloy 3
Disconnect Type	Fusible disconnect switch H, 30 A
Nema Size	2

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
----------------	---

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	60.00 lb(US) (27.216 kg)

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months