

Product data sheet

Specifications



NEMA combination starter, Type S, 60A fusible disconnect, Size 2, 45A, 10HP at 240VAC, 3 phase, 3 pole, Motor Logic SSOLR, 120VAC coil, NEMA 12

8538SDASP4

Product availability: Stock - Normally stocked in distribution facility

Price*: 4,606.00 USD

Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Line Rated Current	45 A
Number Of Poles	3P
Horsepower Rating	10 hp 200 V AC, 3 phase 10 hp 230 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on LED Green indicator off LED
Auxiliary Contacts	2 NO + 2 NC
Thermal Overload Type	Solid state Motor Logic class 10/20 15...45 A
Disconnect Type	Fusible disconnect switch H and K, 60 A, electrical SPDT
Nema Size	2
Height	27.75 in (704.85 mm)
Depth	9.59 in (243.59 mm)
Width	10.5 in (266.70 mm)

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
Product Certifications	UL Listed CSA

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	US10CP121213
Discount Schedule	0CP1
Gtin	785901876427
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.40 in (31.5 cm)
Package 1 Width	14.02 in (35.6 cm)
Package 1 Length	32.09 in (81.5 cm)
Package 1 Weight	50.99 lb(US) (23.13 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Reach Regulation	REACH Declaration
Eu Rohs Directive	Not compliant
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov