

Product data sheet

Specifications

SQUARE D



COMBO STARTER 600VAC 45A NEMA

8539SDW53V81AFF4P1P2TX22

Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz 480 V AC 60 Hz
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	10 hp 230 V AC, 3 phase 25 hp 575 V AC, 3 phase 7.5...10 hp 200 V AC, 3 phase 20...25 hp 460 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Push-button START) Push-button STOP)
Pilot Light	Red indicator on incandescent Green indicator off incandescent
Auxiliary Contacts	2 NO + 2 NC
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal Overload Type	Melting alloy 3
Disconnect Type	Mag-Gard circuit breaker

Environment

Enclosure Type	NEMA 4X glass polyester with external reset
Nema Size	2

Ordering and shipping details

Category	21217-8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

