

Product data sheet

Specifications

SQUARE D



COMBO STARTER 600VAC 135A NEMA

8539SFA14V02P2SX20Y74

! Discontinued

Main

Circuit Breaker Type	KAL
Contactor Application	Non-reversing
Device Short Name	S
Disconnecter Device Type	Thermal magnetic circuit breaker 200 A
Product Or Component Type	Pilot light
Signalling Colour	Green

Complementary

Rated Current	135 A
Auxiliary Contact Composition	2 NO
Depth	10.53 in (267.46 mm)
Device Mounting	Surface
Height	52.5 in (1333.50 mm)
Maximum Horse Power Rating	40 hp 200 V AC 50 hp 230 V AC 100 hp 460 V AC
Nema Size	4
Number Of Poles	3
Number Of Thermal Units Required	3
Product Destination	Circuit breaker KAL
Net Weight	170 lb(US) (77.11 kg)
Reset	With external
Short-Circuit Protection	10000 A AIR
Width	16 in (406.40 mm)

Environment

Nema Degree Of Protection	NEMA 12
Product Certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21214-8538,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	00785901180708
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------