

# Product data sheet

Specifications



## OBSOLETE COMBINATION STARTER

8539SFT43V08C

Price\*: 14,120.00 USD

! Discontinued

### Main

|                      |                        |
|----------------------|------------------------|
| Product              | Combination Starter    |
| Type                 | S                      |
| Control Circuit Type | Common control circuit |

### Complementary

|                         |                                                    |
|-------------------------|----------------------------------------------------|
| Control Circuit Voltage | 208 V AC 60 Hz                                     |
| Starter Type            | Non reversing                                      |
| Number Of Poles         | 3P                                                 |
| Horsepower Rating       | 40 hp 230 V AC, 3 phase<br>40 hp 200 V AC, 3 phase |
| Maximum Voltage Rating  | 600 V AC                                           |
| Control Units           | Selector switch HAND-OFF-AUTO)                     |
| Pilot Light             | No indicator                                       |
| Auxiliary Contacts      | Without                                            |
| Thermal Overload Type   | Melting alloy 3                                    |
| Disconnect Type         | Mag-Gard circuit breaker                           |

### Environment

|                |                                                    |
|----------------|----------------------------------------------------|
| Enclosure Type | NEMA 7/9 Cast Aluminium bolted with external reset |
| Nema Size      | 4                                                  |

### Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |

### Packing Units

|                              |                           |
|------------------------------|---------------------------|
| Unit Type Of Package 1       | PCE                       |
| Number Of Units In Package 1 | 1                         |
| Package 1 Weight             | 185.00 lb(US) (83.915 kg) |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

