

Product data sheet

Specifications

SQUARE D



COMBO STARTER 600VAC 135A NEMA

8539SFW52V08C

Discontinued

Main

Contactor Application	Non-reversing
Device Short Name	S

Complementary

Rated Current	135 A
Depth	11.4 in (289.56 mm)
Device Mounting	Surface
Height	33.5 in (850.90 mm)
Maximum Horse Power Rating	30 hp 200 V AC 60...75 hp 460 V AC 60...100 hp 575 V AC
Nema Size	4
Number Of Poles	3
Number Of Thermal Units Required	3
Product Destination	Circuit breaker KAL3625025M
Net Weight	120 lb(US) (54.43 kg)
Short-Circuit Protection	22000 A AIR
Width	26.31 in (668.27 mm)

Environment

Nema Degree Of Protection	NEMA 4X
Product Certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21217-8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	125.00 lb(US) (56.699 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------