

Product data sheet

Specifications

SQUARE D



NEMA Combination Starter, Type S, 250A thermal magnetic circuit breaker, Size 5, 270A, 3 phase, 208 VAC coil, NEMA 12

8539SGA1V08

 To be discontinued

 To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	208 V AC 60 Hz
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	60 hp 200 V AC, 3 phase 75 hp 230 V AC, 3 phase 150 hp 460 V AC, 3 phase 200 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal Overload Type	Melting alloy 3
Disconnect Type	Thermal magnetic circuit breaker, 250 A

Environment

Enclosure Type	NEMA 12 painted sheet steel without external reset
Nema Size	5

Ordering and shipping details

Category	21215 - 8538,39SG(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Weight	440.00 lb(US) (199.581 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not compliant
