

# Product data sheet

Specifications

SQUARE D



## COMBO STARTER 600VAC 270A NEMA

8539SGG43V03

Discontinued

### Main

Contactor Application	Non-reversing
Device Short Name	S

### Complementary

Rated Current	270 A
Depth	13.72 in (348.49 mm)
Device Mounting	Surface
Height	66 in (1676.40 mm)
Maximum Horse Power Rating	60 hp 230 V AC 125 hp 460 V AC
Nema Size	5
Number Of Poles	3
Number Of Thermal Units Required	3
Product Destination	Circuit breaker KAL3625031M
Net Weight	420 lb(US) (190.51 kg)
Short-Circuit Protection	22000 A AIR
Width	20 in (508.00 mm)

### Environment

Nema Degree Of Protection	NEMA 1
Product Certifications	UL listed file E152395 CCN NKJH7

### Ordering and shipping details

Category	21215-8538,39SG(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications