

Product data sheet

Specifications

SQUARE D



COMBO STARTER 600VAC 270A NEMA

8539SGG43V81AF4H10P1T

Price*: 21,981.00 USD

! Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz 480 V AC 60 Hz
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	60 hp 230 V AC, 3 phase 125 hp 460 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Push-button START) Push-button STOP)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Thermal Overload Type	Solid state Motor Logic class 10
Disconnect Type	Mag-Gard circuit breaker

Environment

Enclosure Type	NEMA 1 painted sheet steel with external reset
Nema Size	5

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications