

# Product data sheet

Specifications

SQUARE D



NEMA Combination Starter, Type S, Mag Guard circuit breaker, Size 6, 540A, 3 phase, 600 VAC coil, NEMA 4X

8539SHW42V07

To be discontinued

To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit

## Complementary

Control Circuit Voltage	550 V AC 50 Hz 600 V AC 60 Hz
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	250 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal Overload Type	Melting alloy 3
Disconnect Type	Mag-Gard circuit breaker

## Environment

Enclosure Type	NEMA 4 painted sheet steel with external reset
Nema Size	6

## Ordering and shipping details

Category	21218 - 8538,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	440.00 lb(US) (199.581 kg)
------------------	----------------------------

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not compliant
-------------------	---------------

---