

Product data sheet

Specifications

SQUARE D



Reversing Contactor, Size 0, 2-Pole, NEMA 12 +Options

8702SBA1V02A1S

Price*: 1,886.00 USD

! Discontinued

Main

Product Type	Contactor
Product Range	Type S
Contactor Type	Reversing

Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	2P
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	1 phase
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	3 momentary push-buttons (FORWARD-REVERSE-STOP)
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	13.74 in (349 mm)
Width	11.89 in (302 mm)
Depth	7.76 in (197 mm)

Environment

Enclosure Type	NEMA 12 painted sheet steel
Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	16.42 lb(US) (7.448 kg)

Contractual warranty

Warranty	18 months
----------	-----------