

Product data sheet

Specifications



NEMA Contactor, Type S, reversing, horizontal, Size 0, 18A, 5 HP at 575 VAC, 3 phase, up to 100 kA, 3 pole, 480 VAC coil, open style

8702SBO4V06

⚠ To be discontinued

⚠ To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|----------------|-----------|
| Product Type | Contactor |
| Product Range | Type S |
| Contactor Type | Reversing |

Complementary

| | |
|------------------------|--|
| Nema Size | 0 |
| Rated Current | 18 A |
| Number Of Poles | 3P |
| Mounting Orientation | Horizontal |
| Wiring Mode | 3 wires |
| Maximum Voltage Rating | 600 V AC |
| Phase | 3 phase |
| Horsepower Rating | 3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC |
| Sccr | Circuit-breaker 70 A maximum, SCCR: 100 kA at 480 V AC Fuse J 60 A maximum, SCCR: 100 kA at 600 V AC Fuse T 60 A maximum, SCCR: 100 kA at 600 V AC Fuse RK1 60 A maximum, SCCR: 100 kA at 600 V AC Fuse RK5 60 A maximum, SCCR: 100 kA at 600 V AC |
| Coil Voltage | 440 V AC 50 Hz 480 V AC 60 Hz |
| Control Circuit Type | Common control circuit |
| Control Units | No control units |
| Pilot Light | No indicator |
| Other Equipment | Fuse not supplied |
| Terminal Type | Screw clamp terminals |
| Height | 5.00 in (127.00 mm) |
| Width | 7.13 in (181.10 mm) |
| Depth | 5.31 in (134.87 mm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

| | |
|----------------|-------------------------|
| Enclosure Type | Not rated (open device) |
| Certifications | UL Listed CSA |

Ordering and shipping details

| | |
|-------------------|------------------------------------|
| Category | 21271 - 8702,36 SA,SB(NOT S*R,T,W) |
| Discount Schedule | CP1 |
| Gtin | 785901724216 |
| Returnability | No |
| Country Of Origin | MX |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.00 in (12.7 cm) |
| Package 1 Width | 7.13 in (18.1 cm) |
| Package 1 Length | 5.31 in (13.5 cm) |
| Package 1 Weight | 11.00 lb(US) (4.99 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation