

Product data sheet

Specifications

SQUARE D



Reversing Contactor, Size 1, 3-Pole, Vertical Open Style +Options

8702SCO7V06X0001

Price*: 1,326.00 USD

! Discontinued

Main

Product Type	Contactor
Product Range	Type S
Contactor Type	Reversing

Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	4P
Mounting Orientation	Vertical
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Coil Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Auxiliary Contacts	1 NC reverse
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	9.21 in (234 mm)
Width	6.42 in (163 mm)
Depth	5.31 in (135 mm)

Environment

Enclosure Type	Not rated (open device)
Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
-------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	11.00 lb(US) (4.99 kg)

Contractual warranty

Warranty	18 months
----------	-----------