

Product data sheet

Specifications

SQUARE D



REVERSING STARTER 240VAC 9A NEMA

8736SAG13V02S

! Discontinued

Main

Device Short Name	S
-------------------	---

Complementary

Depth	7.53 in (191.26 mm)
Device Mounting	Surface
Height	11.88 in (301.75 mm)
Maximum Horse Power Rating	0.34 hp 115 V AC 1 hp 230 V AC
Motor Starter Type	Reversing
Nema Size	00
Number Of Poles	2
Number Of Thermal Units Required	1
Net Weight	17 lb(US) (7.71 kg)
Width	11.88 in (301.75 mm)

Environment

Nema Degree Of Protection	NEMA 1
Product Certifications	NEMA UL Listed

Ordering and shipping details

Category	21271-8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	25.28 lb(US) (11.467 kg)

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months