

# Product data sheet

Specifications



NEMA Starter, Type S, reversing, horizontal, Size 00, 9A, 2 HP at 575 VAC, 5 kA SSCR, 3 phase, 3 pole, melting alloy overload, 120 VAC coil, NEMA 1

8736SAG16V02S

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 989.00 USD

## Main

|               |           |
|---------------|-----------|
| Product Type  | Starter   |
| Product Range | S         |
| Starter Type  | Reversing |

## Complementary

|                        |  |
|------------------------|--|
| Nema Size              | 00   |
| Rated Current          | 9 A  |
| Number Of Poles        | 3P   |
| Mounting Orientation   | Horizontal   |
| Wiring Mode            | 3 wires  |
| Maximum Voltage Rating | 600 V AC   |
| Phase                  | 3 phase  |
| Type Of Overload       | Melting alloy 3  |
| Horsepower Rating      | 1.5 HP 200 V AC<br>1.5 HP 230 V AC<br>2 HP 460 V AC<br>2 HP 575 V AC |
| Sccr                   | Circuit-breaker: 5 kA at 600 V AC<br>Fuse: 5 kA at 600 V AC          |
| Coil Voltage           | 110 V AC 50 Hz<br>120 V AC 60 Hz                                     |
| Control Circuit Type   | Separate control circuit   |
| Control Units          | No control units   |
| Pilot Light            | Without pilot light  |
| Auxiliary Contacts     | Without  |
| Terminal Type          | Screw clamp terminals  |
| Height                 | 11.88 in (301.75 mm)   |
| Width                  | 11.88 in (301.75 mm)   |
| Depth                  | 7.53 in (191.26 mm)  |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environment

|                |                            |
|----------------|----------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
| Certifications | UL Listed<br>CSA           |

## Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US10CP121271 |
| Discount Schedule | 0CP1         |
| Gtin              | 785901903635 |
| Returnability     | No           |
| Country Of Origin | MX           |

## Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type Of Package 1       | PCE                     |
| Number Of Units In Package 1 | 1                       |
| Package 1 Height             | 9.40 in (23.876 cm)     |
| Package 1 Width              | 13.80 in (35.052 cm)    |
| Package 1 Length             | 14.50 in (36.83 cm)     |
| Package 1 Weight             | 20.81 lb(US) (9.439 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

|                           |   |
|---------------------------|---|
| Eu Rohs Directive         | Not compliant   |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information.  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a> |