

# Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 0, 18A, 5 HP at 575 VAC, 5 kA SSCR, 3 phase, 3 pole, melting alloy overload, 120 VAC coil, NEMA 12

8736SBA4V84F4T

! Discontinued

Price\*: 1,800.00 USD

## Main

|               |           |
|---------------|-----------|
| Product Type  | Starter   |
| Product Range | S         |
| Starter Type  | Reversing |

## Complementary

|                        |                                                                    |
|------------------------|--------------------------------------------------------------------|
| Nema Size              | 0                                                                  |
| Rated Current          | 18 A                                                               |
| Number Of Poles        | 3P                                                                 |
| Mounting Orientation   | Horizontal                                                         |
| Wiring Mode            | 3 wires                                                            |
| Maximum Voltage Rating | 600 V AC                                                           |
| Phase                  | 3 phase                                                            |
| Type Of Overload       | Melting alloy 3                                                    |
| Horsepower Rating      | 3 HP 200 V AC<br>3 HP 230 V AC<br>5 HP 460 V AC<br>5 HP 575 V AC   |
| Scrr                   | Circuit-breaker: 5 kA at 600 V AC<br>Fuse: 5 kA at 600 V AC        |
| Coil Voltage           | 208 V AC 60 Hz primary circuit<br>120 V AC 60 Hz secondary circuit |
| Control Circuit Type   | Control circuit transformer                                        |
| Control Units          | No control units                                                   |
| Pilot Light            | Without pilot light                                                |
| Auxiliary Contacts     | Without                                                            |
| Other Equipment        | 2 fuses (primary)                                                  |
| Terminal Type          | Screw clamp terminals                                              |
| Height                 | 13.75 in (349.25 mm)                                               |
| Width                  | 11.88 in (301.75 mm)                                               |
| Depth                  | 7.75 in (196.85 mm)                                                |

## Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                |                             |
|----------------|-----------------------------|
| Enclosure Type | NEMA 12 painted sheet steel |
| Certifications | UL Listed<br>CSA            |

## Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |

## Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type Of Package 1       | PCE                     |
| Number Of Units In Package 1 | 1                       |
| Package 1 Weight             | 17.80 lb(US) (8.074 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|