

# Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 0, 18A, 2 HP at 230 VAC, 5 kA SSCR, 1 phase, 2 pole, melting alloy overload, 120 VAC coil, NEMA 1

8736SBG1V02S

⚠ To be discontinued

⚠ To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

|               |           |
|---------------|-----------|
| Product Type  | Starter   |
| Product Range | S         |
| Starter Type  | Reversing |

## Complementary

|                        |   |
|------------------------|---|
| Nema Size              | 0   |
| Rated Current          | 18 A  |
| Number Of Poles        | 2P  |
| Mounting Orientation   | Horizontal  |
| Wiring Mode            | 3 wires   |
| Maximum Voltage Rating | 600 V AC  |
| Phase                  | 1 phase   |
| Type Of Overload       | Melting alloy 1   |
| Horsepower Rating      | 1 HP 115 V AC<br>2 HP 230 V AC                              |
| Sccr                   | Circuit-breaker: 5 kA at 600 V AC<br>Fuse: 5 kA at 600 V AC |
| Coil Voltage           | 110 V AC 50 Hz<br>120 V AC 60 Hz                            |
| Control Circuit Type   | Separate control circuit                                    |
| Control Units          | No control units  |
| Pilot Light            | Without pilot light   |
| Auxiliary Contacts     | Without   |
| Terminal Type          | Screw clamp terminals                                       |
| Height                 | 11.88 in (301.75 mm)  |
| Width                  | 11.88 in (301.75 mm)  |
| Depth                  | 7.53 in (191.26 mm)   |

## Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                |                            |
|----------------|----------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
| Certifications | UL Listed<br>CSA           |

## Ordering and shipping details

|                   |                                    |
|-------------------|------------------------------------|
| Category          | 21271 - 8702,36 SA,SB(NOT S*R,T,W) |
| Discount Schedule | CP1                                |
| Gtin              | 785901777816                       |
| Returnability     | No                                 |
| Country Of Origin | MX                                 |

## Packing Units

|                              |                          |
|------------------------------|--------------------------|
| Unit Type Of Package 1       | PCE                      |
| Number Of Units In Package 1 | 1                        |
| Package 1 Height             | 11.89 in (30.2 cm)       |
| Package 1 Width              | 11.89 in (30.2 cm)       |
| Package 1 Length             | 7.52 in (19.1 cm)        |
| Package 1 Weight             | 25.21 lb(US) (11.435 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation

---