

# Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 0, 18A, 2 HP at 230 VAC, 5 kA SSCR, 1 phase, 2 pole, melting alloy overload, 240 VAC coil, NEMA 1

8736SBG1V03A1

Discontinued

Price\*: 1,665.00 USD

## Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

## Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	2P
Mounting Orientation	Horizontal
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	1 phase
Type Of Overload	Melting alloy 1
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
Sccr	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	3 momentary push-buttons (FORWARD-REVERSE-STOP)
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	11.88 in (301.75 mm)
Width	11.88 in (301.75 mm)
Depth	7.53 in (191.26 mm)

## Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	UL Listed CSA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	23.78 lb(US) (10.786 kg)

## Contractual warranty

Warranty	18 months
----------	-----------