

# Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 0, 18A, 5 HP at 575 VAC, 5 kA SSCR, 3 phase, 3 pole, melting alloy overload, 240 VAC coil, NEMA 1

8736SBG4V03A20G12

! Discontinued

Price\*: 1,508.00 USD

## Main

|               |           |
|---------------|-----------|
| Product Type  | Starter   |
| Product Range | S         |
| Starter Type  | Reversing |

## Complementary

|                        |                                                                  |
|------------------------|------------------------------------------------------------------|
| Nema Size              | 0                                                                |
| Rated Current          | 18 A                                                             |
| Number Of Poles        | 3P                                                               |
| Mounting Orientation   | Horizontal                                                       |
| Wiring Mode            | 3 wires                                                          |
| Maximum Voltage Rating | 600 V AC                                                         |
| Phase                  | 3 phase                                                          |
| Type Of Overload       | Melting alloy 3                                                  |
| Horsepower Rating      | 3 HP 200 V AC<br>3 HP 230 V AC<br>5 HP 460 V AC<br>5 HP 575 V AC |
| Sccr                   | Circuit-breaker: 5 kA at 600 V AC<br>Fuse: 5 kA at 600 V AC      |
| Coil Voltage           | 220 V AC 50 Hz<br>240 V AC 60 Hz                                 |
| Control Circuit Type   | Common control circuit                                           |
| Control Units          | 3 momentary push-buttons (FORWARD-REVERSE-STOP)                  |
| Pilot Light            | Without pilot light                                              |
| Auxiliary Contacts     | Without                                                          |
| Terminal Type          | Screw clamp terminals                                            |
| Height                 | 11.88 in (301.75 mm)                                             |
| Width                  | 11.88 in (301.75 mm)                                             |
| Depth                  | 7.53 in (191.26 mm)                                              |

## Environment

|                |                            |
|----------------|----------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
|----------------|----------------------------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                |                  |
|----------------|------------------|
| Certifications | UL Listed<br>CSA |
|----------------|------------------|

## Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |
| Country Of Origin | US  |

## Packing Units

|                              |                          |
|------------------------------|--------------------------|
| Unit Type Of Package 1       | PCE                      |
| Number Of Units In Package 1 | 1                        |
| Package 1 Weight             | 23.78 lb(US) (10.786 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|