

# Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 0, 18A, 5 HP at 575 VAC, 5 kA SSCR, 3 phase, 3 pole, ambient compensated bimetal, 120 VAC coil, open

8736SBO4V02BS

Discontinued

## Main

|               |           |
|---------------|-----------|
| Product Type  | Starter   |
| Product Range | S         |
| Starter Type  | Reversing |

## Complementary

|                        |  |
|------------------------|--|
| Nema Size              | 0  |
| Rated Current          | 18 A   |
| Number Of Poles        | 3P   |
| Maximum Voltage Rating | 600 V AC   |
| Phase                  | 3 phase  |
| Type Of Overload       | Ambient compensated bimetallic                                   |
| Horsepower Rating      | 3 HP 200 V AC<br>3 HP 230 V AC<br>5 HP 460 V AC<br>5 HP 575 V AC |
| Coil Voltage           | 110 V AC 50 Hz<br>120 V AC 60 Hz                                 |
| Control Circuit Type   | Separate control circuit   |
| Control Units          | No control units   |
| Terminal Type          | Screw clamp terminals  |

## Environment

|                |                          |
|----------------|--------------------------|
| Enclosure Type | Not rated (open device)  |
| Certifications | NEMA<br>UL Listed<br>CSA |

## Ordering and shipping details

|                   |                                  |
|-------------------|----------------------------------|
| Category          | 21271-8702,36 SA,SB(NOT S*R,T,W) |
| Discount Schedule | CP1                              |
| Returnability     | No                               |
| Country Of Origin | MX                               |

## Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |                        |
|------------------------------|------------------------|
| Unit Type Of Package 1       | PCE                    |
| Number Of Units In Package 1 | 1                      |
| Package 1 Weight             | 7.78 lb(US) (3.529 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|