

Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 0, 18A, 5 HP at 575 VAC, 5 kA SSCR, 3 phase, 3 pole, melting alloy overload, 120 VAC coil, open

8736SBO4V02SX0202

! Discontinued

Price*: 1,724.00 USD

Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	3P
Mounting Orientation	Horizontal
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
Sccr	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	2 NC reverse 2 NC forward
Terminal Type	Screw clamp terminals
Height	6.91 in (175.51 mm)
Width	8.15 in (207.01 mm)
Depth	5.31 in (134.87 mm)

Environment

Enclosure Type	Not rated (open device)
----------------	-------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Certifications	UL Listed CSA
----------------	------------------

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	7.94 lb(US) (3.602 kg)

Contractual warranty

Warranty	18 months
----------	-----------