

Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 1, 27A, 10 HP at 575 VAC, 5 kA SSCR, 3 phase, 3 pole, non compensated bimetal, 120 VAC coil, NEMA 1

8736SCG8V02B2S

Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Non-compensated bimetallic
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Terminal Type	Screw clamp terminals

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	CSA NEMA UL Listed

Ordering and shipping details

Category	21272-8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	25.70 lb(US) (11.657 kg)

Contractual warranty

Warranty	18 months
----------	-----------