

Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, vertical, Size 4, 135A, 100 HP at 575 VAC, up to 100 kA SCCR, 3 phase, 3 pole, TeSys T SSOLR, 120 VAC coil, open

8736SFO1V02H656S

! Discontinued

! Discontinued on: Oct 11, 2021

Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

Complementary

Nema Size	4
Rated Current	135 A
Number Of Poles	3P
Mounting Orientation	Vertical
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Solid state TeSys T
Horsepower Rating	40 HP 200 V AC 50 HP 230 V AC 100 HP 460 V AC 100 HP 575 V AC
Sccr	Circuit-breaker 225 A maximum: 100 kA at 480 V AC Fuse J 200 A maximum: 100 kA at 600 V AC Fuse T 200 A maximum: 100 kA at 600 V AC Fuse RK1 200 A maximum: 100 kA at 600 V AC Fuse RK5 200 A maximum: 100 kA at 600 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	26.81 in (680.97 mm)
Width	7.97 in (202.44 mm)
Depth	7.00 in (177.80 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Enclosure Type	Not rated (open device)
Certifications	UL Listed CSA

Ordering and shipping details

Category	21273-8702,36 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------