

Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 5, 270A, 200 HP at 575 VAC, 10 kA SCCR, 3 phase, 3 pole, melting alloy overload, 120 V coil, NEMA 1

8736SGG3V84FF4P1TX1100

! Discontinued

Price*: 24,345.00 USD

Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

Complementary

Nema Size	5
Rated Current	270 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	75 HP 200 V AC 100 HP 230 V AC 200 HP 460 V AC 200 HP 575 V AC
Coil Voltage	208 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Control Circuit Type	Control circuit transformer
Control Units	No control units
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	1 NO + 1 NC forward
Other Equipment	1 fuse (primary), 1 fuse (secondary)
Terminal Type	Screw clamp terminals

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	UL Listed NEMA CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	US
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------