

# Product data sheet

Specifications

SQUARE D



## REVERSING COMBO STARTER 240VAC 18A NEM

8738SBA12V03

 To be discontinued on: Sep 30, 2024

 To be discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit
Control Units	No control units
Enclosure Type	NEMA 12 painted sheet steel without external reset
Auxiliary Contacts	Without
Horsepower Rating	3 hp 200 V AC, 3 phase 3 hp 230 V AC, 3 phase
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Nema Size	0
Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Pilot Light	No indicator
Starter Type	Reversing
Overload Type	melting alloy
Number Of Thermal Units Required	3
Disconnect Type	Fusible disconnect H, 30 A

### Ordering and shipping details

Category	21291 - 8738,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	34.11 lb(US) (15.473 kg)

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation

---