

# Product data sheet

Specifications

SQUARE D



## REVERSING COMBO STARTER 600VAC 27A NEM

8738SCA14V81A1F4T

Price\*: 3,780.00 USD

! Discontinued

### Main

|                                  |                                                                    |
|----------------------------------|--------------------------------------------------------------------|
| Product                          | Combination Starter                                                |
| Type                             | S                                                                  |
| Control Circuit Type             | Control circuit transformer                                        |
| Control Circuit Fusing           | 2 fuses primary circuit                                            |
| Control Units                    | Push-button FORWARD)<br>Push-button REVERSE)<br>Push-button STOP)  |
| Enclosure Type                   | NEMA 12 painted sheet steel without external reset                 |
| Auxiliary Contacts               | Without                                                            |
| Horsepower Rating                | 10 hp 460 V AC, 3 phase<br>10 hp 575 V AC, 3 phase                 |
| Number Of Poles                  | 3P                                                                 |
| Maximum Voltage Rating           | 600 V AC                                                           |
| Nema Size                        | 1                                                                  |
| Control Circuit Voltage          | 120 V AC 60 Hz secondary circuit<br>480 V AC 60 Hz primary circuit |
| Pilot Light                      | No indicator                                                       |
| Starter Type                     | Reversing                                                          |
| Overload Type                    | melting alloy                                                      |
| Number Of Thermal Units Required | 3                                                                  |
| Disconnect Type                  | Fusible disconnect H, 30 A                                         |

### Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |

### Packing Units

|                              |                          |
|------------------------------|--------------------------|
| Unit Type Of Package 1       | PCE                      |
| Number Of Units In Package 1 | 1                        |
| Package 1 Weight             | 57.00 lb(US) (25.855 kg) |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

