

Product data sheet

Specifications

SQUARE D



REVERSING COMBO STARTER 600VAC 270A NE

8738SGA11V06

 Discontinued on: Oct 12, 2021

 Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit
Control Units	No control units
Enclosure Type	NEMA 12 painted sheet steel without external reset
Auxiliary Contacts	Without
Horsepower Rating	75 hp 200 V AC, 3 phase 100 hp 230 V AC, 3 phase 200 hp 460 V AC, 3 phase 200 hp 575 V AC, 3 phase
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Nema Size	5
Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Pilot Light	No indicator
Starter Type	Reversing
Overload Type	melting alloy
Number Of Thermal Units Required	3
Disconnect Type	Non-fusible disconnect

Ordering and shipping details

Category	21294-8738,39SG(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.p65warnings.ca.gov
