

Product data sheet

Specifications

SQUARE D



REVERSING COMBO STARTER 600VAC 18ANEM

8739SBW51V02S

! Discontinued

Main

Device Short Name	S
-------------------	---

Complementary

Depth	11.4 in (289.56 mm)
Device Mounting	Surface
Height	27 in (685.80 mm)
Maximum Horse Power Rating	0.25...0.34 hp 200/230 V AC 0.25...1 hp 460/575 V AC
Motor Starter Type	Reversing
Nema Size	0
Number Of Poles	3
Number Of Thermal Units Required	3
Product Destination	Circuit breaker GJL36003M01
Width	25.25 in (641.35 mm)

Environment

Nema Degree Of Protection	NEMA 4X
Product Certifications	NEMA UL Listed

Ordering and shipping details

Category	21297-8738,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	57.00 lb(US) (25.855 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

