

Product data sheet

Specifications

SQUARE D



REVERSING COMBO STARTER 600VAC 27ANEM

8739SCG43V02S

! Discontinued

Main

Circuit Breaker Type	GJL36015M03
Device Short Name	S

Complementary

Depth	8.34 in (211.84 mm)
Device Mounting	Surface
Height	23 in (584.20 mm)
Maximum Horse Power Rating	1.5...3 hp 200/230 V AC 5...7.5 hp 460 V AC 5...10 hp 575 V AC
Motor Starter Type	Reversing
Nema Size	1
Number Of Poles	3
Number Of Thermal Units Required	3
Product Destination	Circuit breaker GJL36015M03
Net Weight	49 lb(US) (22.23 kg)
Width	13.75 in (349.25 mm)

Environment

Nema Degree Of Protection	NEMA 1
Product Certifications	NEMA UL Listed

Ordering and shipping details

Category	21292-8738,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	55.00 lb(US) (24.948 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------