

Product data sheet

Specifications

SQUARE D



REVERSING COMBO STARTER 600VAC 27ANEM

8739SCW43V06C14

! Discontinued

Main

Circuit Breaker Type	GJL36015M03
Device Short Name	S

Complementary

Control Type	selector switch FORWARD-OFF-REVERSE
Depth	8.34 in (211.84 mm)
Device Mounting	Surface
Height	25.19 in (639.83 mm)
Maximum Horse Power Rating	1.5...3 hp 200/230 V AC 5...7.5 hp 460 V AC 5...10 hp 575 V AC
Motor Starter Type	Reversing
Nema Size	1
Number Of Poles	3
Number Of Thermal Units Required	3
Product Destination	Circuit breaker GJL36015M03
Net Weight	52 lb(US) (23.59 kg)
Width	13.75 in (349.25 mm)

Environment

Nema Degree Of Protection	NEMA 4/4X
Product Certifications	NEMA UL Listed

Ordering and shipping details

Category	21297-8738,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	60.00 lb(US) (27.216 kg)
------------------	--------------------------

Contractual warranty

Warranty	18 months
----------	-----------