

Product data sheet

Specifications

SQUARE D



REVERSING COMBO STARTER 600VAC 135ANE

8739SFA43V06

! Discontinued

Main

Device Short Name	S
-------------------	---

Complementary

Rated Current	135 A
Depth	10.59 in (268.99 mm)
Device Mounting	Surface
Height	45 in (1143.00 mm)
Maximum Horse Power Rating	40 hp 200/230 V AC
Motor Starter Type	Reversing
Nema Size	4
Number Of Poles	3
Number Of Thermal Units Required	3
Product Destination	Circuit breaker KAL3625026M
Reset	Without external
Width	18.5 in (469.90 mm)

Environment

Nema Degree Of Protection	NEMA 12
Product Certifications	UL Listed NEMA

Ordering and shipping details

Category	21293-8738,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	255.00 lb(US) (115.666 kg)

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months