# **Product data sheet**

Specifications



# Contactor, Type L, multipole lighting, electrically held, 30A, 10 pole, 600 V, 110/120 VAC 50/60 Hz coil, NEMA 3R/12

8903LA1000V81CFF4T

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Or Component Type	Electrically Held Lighting Contactor	
Range Of Product	8903L	
Control Circuit	Control circuit transformer	

### Complementary

e emprementar j		
Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit	
Inrush Power In Va	180 VA 60 Hz	
Hold-In Power Consumption In Va	35 VA 60 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	10P 10 NO	
Control Unit	Selector switch HAND-OFF-AUTO)	
Pilot Light	No indicator	
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit	
Electrical Connection	Screw-clamp terminals	
Height	13.50 in (343 mm)	
Depth	7.76 in (197 mm)	
Width	11.89 in (302 mm)	

#### Environment

Enclosure Type	NEMA 12 painted sheet steel surface	
Product Certifications	UL Listed CSA	

### Ordering and shipping details

Category	21321 - 8903 L (NOT LX)	
Discount Schedule	CP1	
Returnability	No	
Country Of Origin	MX	

### **Packing Units**

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Weight	40.08 lb(US) (18.18 kg)	

# **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov