Product data sheet

Specifications



8903L electrically held lighting contactor, 3 P, 3 NO, 30 A, 600 V, 277 V 60 Hz coil, NEMA 3R/12

8903LA30V04

() Discontinued on: Dec 12, 2019

(!) End-of-service on: Oct 15, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Product Or Component Type | Electrically Held Lighting Contactor |
|---------------------------|--------------------------------------|
| Range Of Product | 8903L |
| Control Circuit | Separate control circuit |

Complementary

| complementary | |
|---------------------------------|-----------------------------------|
| Control Circuit Voltage | 277 V AC 60 Hz |
| Inrush Power In Va | 150 VA 60 Hz |
| Hold-In Power Consumption In Va | 30 VA 60 Hz |
| Current Rating | 20 A tungsten 30 A fluorescent |
| Number Of Poles | 3P 3 NO |
| Control Unit | No control units |
| Pilot Light | No indicator |
| Electrical Connection | Screw-clamp terminals |
| Height | 15.75 in (400 mm) |
| Depth | 8.50 in (216 mm) |
| Width | 8.11 in (206 mm) |

Environment

| Enclosure Type | NEMA 12 painted sheet steel surface |
|------------------------|-------------------------------------|
| Product Certifications | UL Listed CSA |

Ordering and shipping details

| Category | 21321 - 8903 L (NOT LX) |
|-------------------|-------------------------|
| Discount Schedule | CP1 |
| Gtin | 785901772675 |
| Returnability | No |
| Country Of Origin | МХ |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 15.75 in (40 cm) |
| Package 1 Width | 8.11 in (20.6 cm) |
| Package 1 Length | 8.50 in (21.6 cm) |
| Package 1 Weight | 21.78 lb(US) (9.88 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

Certifications & Standards

| Eu Rohs Directive | Compliant EU RoHS Declaration |
|--------------------------|---|
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |