Product data sheet

Specifications



8903L electrically held lighting contactor, 6 P, 6 NO, 30 A, 600 V, 110/120 V 50/60 Hz coil, NEMA 3R/12, selector switch

8903LA60V02C

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,538.00 USD

Main

mann		
Product Or Component Type	Electrically Held Lighting Contactor	
Range Of Product	8903L	
Control Circuit	Separate control circuit	

Complementary

Complementary		
Control Circuit Voltage	110 V AC 50 Hz	
	120 V AC 60 Hz	
Inrush Power In Va	150 VA 60 Hz	
	150 VA 50 Hz	
Hold-In Power Consumption In Va	30 VA 60 Hz	
	30 VA 50 Hz	
Current Rating	20 A tungsten	
	30 A fluorescent	
Number Of Poles	6P 6 NO	
Control Unit	Selector switch HAND-OFF-AUTO)	
Pilot Light	No indicator	
Electrical Connection	Screw-clamp terminals	
Height	13.50 in (343 mm)	
Depth	7.76 in (197 mm)	
Width	11.89 in (302 mm)	

Environment

Enclosure Type	NEMA 12 painted sheet steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)	
Discount Schedule	CP1	
Gtin	785901765516	
Returnability	No	
Country Of Origin	MX	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.50 in (34.3 cm)
Package 1 Width	11.89 in (30.2 cm)
Package 1 Length	7.76 in (19.7 cm)
Package 1 Weight	22.00 lb(US) (9.98 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov