





Contactor, Type L, multipole lighting, electrically held, 30A, 12 pole, 600V, 110/120VAC 50/60Hz coil, NEMA 1

8903LG1200V02

Product availability: Stock - Normally stocked in distribution facility

Price*: 1,529.00 USD

Main

Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Separate control circuit

Complementary

110 V AC 50 Hz 120 V AC 60 Hz
180 VA 60 Hz 170 VA 50 Hz
35 VA 60 Hz 35 VA 50 Hz
20 A tungsten 30 A fluorescent
12P 12 NO
No control units
No indicator
Screw-clamp terminals
12.68 in (322 mm)
6.02 in (153 mm)
7.80 in (198 mm)
11.00 lb(US) (4.99 kg)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	US10CP121321
Discount Schedule	0CP1
Gtin	785901851615
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin MX

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.20 in (18.3 cm)
Package 1 Width	8.31 in (21.1 cm)
Package 1 Length	13.70 in (34.8 cm)
Package 1 Weight	11.07 lb(US) (5.02 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	50
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	553.50 lb(US) (251.062 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
Ø	Toxic Heavy Metal Free
②	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free
②	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Dimensions Drawings

Approximate Dimensions

