





Contactor, Type L, multipole lighting, electrically held, 30A, 12 pole, 600 V, 277 VAC 60 Hz coil, NEMA 1, +option

8903LG1200V04CP1

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Separate control circuit

## Complementary

Control Circuit Voltage	277 V AC 60 Hz
Inrush Power In Va	180 VA 60 Hz
Hold-In Power Consumption In Va	35 VA 60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	12P 12 NO
Control Unit	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Electrical Connection	Screw-clamp terminals
Height	11.89 in (302 mm)
Depth	7.44 in (189 mm)
Width	11.89 in (302 mm)

### **Environment**

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed CSA

## Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	11.89 in (30.2 cm)
Package 1 Width	11.89 in (30.2 cm)
Package 1 Length	7.44 in (18.9 cm)
Package 1 Weight	22.44 lb(US) (10.18 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

# Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>Ø</b>	Mercury Free
<b>9</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free
<b>9</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations