

# Product data sheet

Specifications

SQUARE D



## LIGHTING CONTACTOR 600VAC 30A L

8903LG1200V04G10

Price\*: 1,710.00 USD

! Discontinued

### Main

Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Separate control circuit

### Complementary

Control Circuit Voltage	277 V AC 60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	12P 12 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical Connection	Screw-clamp terminals

### Environment

Enclosure Type	NEMA 1 painted sheet steel surface photoelectric receptacle without cell
Product Certifications	UL Listed CSA

### Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	22.00 lb(US) (9.98 kg)

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications