





(!) Discontinued

8903L electrically held lighting contactor, 6 P, 3 NO, 3 NC, 30 A, 600 V, 110/120 V 50/60 Hz coil, NEMA 1

8903LG33V02

(!) Discontinued on: Oct 15, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Product Or Component Type	Electrically Held Lighting Contactor	
Range Of Product	8903L	
Control Circuit	Separate control circuit	

## Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz	
Inrush Power In Va	150 VA 60 Hz 150 VA 50 Hz	
Hold-In Power Consumption In Va	Va 30 VA 60 Hz 30 VA 50 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	6P 3 NO + 3 NC	
Control Unit	No control units	
Pilot Light	No indicator	
Electrical Connection	Screw-clamp terminals	
Height	12.68 in (322 mm)	
Depth	6.02 in (153 mm)	
Width	7.80 in (198 mm)	

### **Environment**

Enclosure Type	NEMA 1 painted sheet steel surface
<b>Product Certifications</b>	UL Listed CSA

## Ordering and shipping details

Category	US10CP121321	
Discount Schedule	0CP1	
Returnability	No	
Country Of Origin	MX	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.50 in (19.05 cm)
Package 1 Width	8.00 in (20.32 cm)
Package 1 Length	13.50 in (34.29 cm)
Package 1 Weight	12.52 lb(US) (5.677 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>9</b>	Mercury Free
<b>9</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free
<b>⊘</b>	Halogen Free Plastic Parts Product

### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile