# **Product data sheet**

Specifications

#### SQUARE D





## Contactor, Type L, multipole lighting, electrically held, 30A, 6 pole, 600V, 110/120VAC 50/60Hz coil, open style

8903LO60V02

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 746.00 USD

#### Main

Main	
Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Separate control circuit

#### Complementary

Complementary	
Control Circuit Voltage	110 V AC 50 Hz
	120 V AC 60 Hz
Inrush Power In Va	150 VA 60 Hz
	140 VA 50 Hz
Hold-In Power Consumption In Va	30 VA 60 Hz
	30 VA 50 Hz
Current Rating	20 A tungsten
	30 A fluorescent
Number Of Poles	6P 6 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical Connection	Screw-clamp terminals
Height	5.00 in (127 mm)
Depth	3.11 in (79 mm)
Width	4.25 in (108 mm)

## Environment

Enclosure Type	Not rated (open device)
Product Certifications	UL Listed CSA

#### Ordering and shipping details

Category	US10CP121321
Discount Schedule	0CP1
Gtin	785901851721
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.49 in (11.4 cm)
Package 1 Width	5.98 in (15.2 cm)
Package 1 Length	7.01 in (17.8 cm)
Package 1 Weight	3.26 lb(US) (1.48 kg)

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations